Lovibond® Colour Measurement Tintometer® Group



AF509C for Marine Diesel Fuel Type F76

Kit for Visual Colour Grading of Type F76 Marine Diesel Fuels according to ASTM Colour



- Fast, Economical & Portable Visual Matching
- Two-Field Vision for Accurate Results
- Ability to Guarantee Constant Lighting Conditions

Part Number: 415090

Quick, On-site Colour Measurement

This special kit enables you to quickly measure the colour of type F76 marine diesel fuels according to a limited range of the ASTM Colour Scale. It is designed to ensure that the correct fuel is used in motor vessels running with type F76 diesel, thereby avoiding errors in fuel use that can result in expensive corrective maintenance. The test is based on a direct colour match between the sample and a test disc containing ASTM Color standards, enabling you to accept or reject the diesel fuel in a matter of minutes.

Easy Dertermination

The Lovibond® AF 509/C includes a test disc containing a limited range of ASTM Color standards (1 - 5 units as opposed to the full range of 0.5 - 8 units). This is sufficient for this purpose since type F76 fuel has a target colour of 3.5 ASTM Color and reduces the options for you to chose from.

Fast, Economical & Portable Visual Matching

The Comparator 2000+ is a flexible, modular system for Visual Colour Grading. Using a suitable comparator instrument and glass disc, you can quickly visually match the sample directly against the calibrated, colour stable glass standards.

Two-Field Vision for Accurate Results

Lovibond® comparator instruments include an integrated prism which causes the sample and comparison fields to overlap, allowing enhanced colour discrimination and matching. The prism is ultrasonically sealed to prevent contamination of the optics. Each individually graded glass standard represents a discrete step on the measurement range (as opposed to a continuous graduation), aiding colour discrimination and allowing great accuracy of results.

Ability to Guarantee Constant Lighting Conditions

An optional item for the Comparator 2000+ is the Daylight 2000 Lighting Unit. This is a standardised light source which guarantees you a constant lighting condition for accurate colour grading. This is particularly useful when the sample is very pale in colour. By using a Lovibond® lighting unit, you can confident of uniform lighting conditions for colour matching, 24 hours a day and irrespective of ambient lighting.

Extended Shelf Life

The unique feature of Lovibond® test discs is that they incorporate coloured glass standards that are colour stable and not affected by UV light or extreme environmental conditions.

Please note, we cannot guarantee compatability of discontinued Lovibond® Comparator 1000 disks with the Lovibond® 2000+ Comparator.

Industry

Oil and Gas

Application

Petroleum Oils and Waxes

AF509C for Marine Diesel Fuel Type F76

The Comparator 2000+ is an easy-to-use, entry level colour measurement system that compares the colour of the sample directly against

the colour of glass in a disc. All you need to do is rotate the disc to get the closest result to the scale.

Technical Data

Applicable Standard

ASTM D1500 ASTM D6045 ISO 2049

Colour Type Transparent
Portability Portable

Delivery Scope

- Sturdy Case Including
- 1 x Lovibond 2000+ Comparator
- 1 x 4/81 ASTM Diesel Fuel Disc Precalibrated to 1, 2, 3, 4.5, 4, 4.5, 5
- 2 x W680.OG.33mm Cell
- 1 x Kit Instructions

Tintometer GmbH

Lovibond® Water Testing Schleefstraße 8-12 44287 Dortmund Tel.: +49 (0)231/94510-0 sales@lovibond.com www.lovibond.com Germany

Tintometer Brazil

Caixa Postal: 271 CEP: 13201-970 Jundiaí – SP Tel.: +55 (11) 3230-6410 sales@lovibond.us

www.lovibond.com.br Brazil

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com

UK

Tintometer Inc.

6456 Parkland Drive Sarasota, FL 34243 Tel: 941.756.6410 Fax: 941.727.9654 sales@lovibond.us www.lovibond.us USA

Tintometer China 9F, SOHO II C. No.9 Guanghualu,

Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer India Pvt. Ltd.

India

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor Sanathnagar Industrial Estate, Hyderabad, 500018 Telangana Tel: +91 (0) 40 23883300 Toll Free: 1 800 599 3891/ 3892 indiaoffice@lovibond.in www.lovibondwater.in

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard, Lebuh Nilam 2, Bandar Bukit Tinggi, Klang, 41200, Selangor D.E Tel.: +60 (0)3 3325 2285/6 Fax: +60 (0)3 3325 2287 lovibond.asia@tintometer.com www.lovibond.com Malaysia

Tintometer Spain

Postbox: 24047 08080 Barcelona Tel.: +34 661 606 770 sales@tintometer.es www.lovibond.com Spain