

# Lovibond® Water Testing Tintometer® Group



## EC2000 Ecomparator, Platino Cobalto

Colour measurement of water



- Immediate & Accurate
- Straight from the Box
- Guaranteed Agreement with International Standards
- Display Results with On-Screen Colour and Numerical Options

Artigo No: 162010

### Dual Ability to View Colour Comparison

- On-screen colour
- On-screen numerical display

### Easy Transition from Visual to Electronic Measurements

Some colour graders who are used to the traditional comparator series sometimes find the upgrade to an electronic system daunting. The assurance of relying on physical colour difference is diminished. This transition has now been made easy.

### Touch Screen Technology

Enables you to easily programme the instruments with instinctive menus on screen.

### Programmable Settings

You can set language\*, date and time, view preferences and create projects with individual tolerance settings.

### On-Screen Warning System

You can react immediately to results that might be out of tolerance with immediate information on the sample.

- Within tolerance = green
- Outside tolerance = red
- On border of tolerance = amber

### User Friendly Ergonomics and Intuitive Interface

You are guaranteed to be up and running quickly and easily supported.

### Easy storage and sharing of results

Large data storage (> 20,000 readings) and USB connectivity ensure your results can be stored and easily shared.

### Single Scale Measurement

The EC 2000 Pt Co provides you an individual scale to measure Platinum Cobalt/Hazen/Apha Colour (ASTM D 1209).

\* Supported languages: English, French, German, Spanish, Italian, Chinese, Japanese, Russian.

## Indústria

Indústria de Alimentos e Bebidas | Indústria Farmacêutica |  
Indústria Química | Óleo e Gás

## Aplicação

Farmacêuticos e Cosméticos | Óleos e Gorduras Comestíveis |  
Óleos e Graxas de Petróleo | Químicos

## EC2000 Ecomparator, Platino Cobalto

Advance from visual (subjective) to electronic (objective) colour  
measurement.

High precision with 50 mm cuvette path length!

## Dados Técnicos

<b>Tipo de Cor</b>	Transparent
<b>Display</b>	Tamanho: 3.5 polegadas; resolução: 320 x 240; Cor: 24 Bit (Cor verdadeira)
<b>Interfaces</b>	USB
<b>Armazenamento Interno</b>	> 20000 medições
<b>Fonte de Alimentação</b>	USB 2.0 (conector mini USB) 4 pilhas (AA)
<b>Portabilidade</b>	Portátil
<b>Tela Sensível ao Toque</b>	Não
<b>Idiomas da Interface do Usuário</b>	Alemão, Inglês, Francês, Espanhol, Italiano, Russo, Chinês, Japonês
<b>Dimensões</b>	106 x 57 x 210 mm

## Texto do Escopo de Entrega

- Instrument in carrying case
- Power Supply (UK, EU, US Plug)
- USB Cable
- 4 AA Batteries
- Liquid Reference Standard 1
- Liquid Reference Standard 2
- Glass cuvette
- Glass standard
- CD with Software (Windows®)
- Instruction Manual

## Acessórios

Título	Artigo No
Padrão líquido Cobalto platina número de cor 0 - 500 ml	133991
Padrão líquido Platinum-cobalto número de cor 15 - 500 ml	134160
Padrão líquido Cobalto platina número de cor 30 - 500 ml	134170
Padrão líquido Cobalto platina número de cor 15 - 60 ml	135049
Padrão líquido Cobalto platina número de cor 0 - 60 ml	135059
10001723	190620
Cabo USB 2.0 A - Conector Micro B	190630
Cuvetes de plástico descartáveis de 50 mm	352101

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Alemanha

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
Reino Unido

### Tintometer China

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malásia

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brasil

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
EUA

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
Índia

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Espanha

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies