

Lovibond® Colour Measurement Tintometer® Group



Gardner Comparator (AF228)

Gardner Scale, 3-Field Visual Measurement



- Compact, Visual Measurement System for Single Scale Measurements
- Self-Contained, Includes Everything Needed to Measure the Scale
- Easy-To-Use, Fast & Accurate
- 3-Field Viewing for Optimum Accuracy

Part Number: 345010

Accurate Determination of the Gardner Scale

The AF 228 incorporates 18 glass standards which make up the scale in a pair of discs

Fast Determination of Colour Value

You can directly compare the sample with the colour values for quick results.

Easy to Achieve Optimum Colour Accuracy

The advantage of a 3-section field of view is that the sample and two consecutive glasses on the colour scale are viewed simultaneously, making it easier and quicker for you to achieve the ideal colour match.

Facilitates Tolerance Level Setting

For rapid colour grading within predetermined colour limits, the glass standards can be set to the two limiting colours so that it is easy to check that the sample is within tolerance.

Guaranteed Constant Lighting Conditions

In the instruments, the tungsten halogen light source is colour corrected to CIE standard illuminant C*, which guarantees constant lighting conditions for colour grading.

Compliance to Standards

Each Comparator 3000 is supplied with the correct cells for the appropriate path length determined by the standard.

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Oil and Gas

Application

Chemicals | Edible Oils and Fats | Petroleum Oils and Waxes

Gardner Comparator (AF228)

A 3-field instrument for visually determining the colour of petroleum oils & waxes, chemicals and edible oils & fats samples according to the Gardner scale by direct comparison with coloured glass filters.

Technical Data

Applicable Standard	ASTM D509 ASTM D1544 ASTM D6166
Colour Type	Transparent
Portability	Benchtop

Delivery Scope

- **Comparator 3000**
- **2 x Glass Discs**
 - 4/30-1 (left hand) 1, 3, 5, 7, 9, 11, 13, 15, 17
 - 4/30-2 (right hand) 2, 4, 6, 8, 10, 12, 14, 16, 18
- **2 x Test Tubes 10.65mm diameter**

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies