

Lovibond® Colour Measurement Tintometer® Group



AF327 Pt-Co/Hazen/APHA Colour, Low Range, 0 - 70 mg

Visual Colour Grading of Platinum-Cobalt/Hazen/APHA Colour (Range 0 - 70 mg)



- Complies with the Path Length Requirements of ASTM D 1209,
- Fast, Economical & Portable Visual Matching
- Two-Field Vision for Accurate Results
- Ability to Guarantee Constant Lighting Conditions

Part Number: 433270

Enables You to Comply to ASTM 1209

The Lovibond® AF327 is a special kit for visual colour grading of Platinum-Cobalt/Hazen/APHA Colour over the range 0 - 70 mg Pt/l. It enables you to comply with the path length requirements of ASTM D 1209, which specifies a system for colour comparison where a 100 ml column of sample 275 - 295 mm in length is matched with Platinum-Cobalt solutions.

Fast, Economical & Portable Visual Matching

The Comparator 2000+ is a flexible, modular system for Visual Colour Grading. Using a suitable comparator instrument and glass disc, you can quickly visually match the sample directly against the calibrated, colour stable glass standards.

Two-Field Vision for Accurate Results

Lovibond® comparator instruments include an integrated prism which causes the sample and comparison fields to overlap, allowing enhanced colour discrimination and matching. The prism is ultrasonically sealed to prevent contamination of the optics. Each individually graded glass standard represents a discrete step on the measurement range (as opposed to a continuous graduation), aiding colour discrimination and allowing great accuracy of results.

Ability to Guarantee Constant Lighting Conditions

An optional item for the Comparator 2000+ is the Daylight 2000 Lighting Unit. This is a standardised light source which guarantees you a constant lighting condition for accurate colour grading. This is particularly useful when the sample is very pale in colour. By using a Lovi-

bond® lighting unit, you can be confident of uniform lighting conditions for colour matching, 24 hours a day and irrespective of ambient lighting.

Extended Shelf Life

The unique feature of Lovibond® test discs is that they incorporate coloured glass standards that are colour stable and not affected by UV light or extreme environmental conditions.

Please note, we cannot guarantee compatibility of discontinued Lovibond® Comparator 1000 disks with the Lovibond® 2000+ Comparator.

Industry

Chemical Industry | Food and Beverage Industry | Oil and Gas | Pharmaceutical Industry

Application

Chemicals | Edible Oils and Fats | Petroleum Oils and Waxes | Waste-Water Treatment

AF327 Pt-Co/Hazen/APHA Colour, Low Range, 0 - 70 mg

The Lovibond® AF327 is a special kit for visual colour grading of Platinum-Cobalt/Hazen/APHA Colour over the range 0 - 70 mg Pt/l. It enables you to comply with the path length requirements of ASTM D 1209, which specifies a system for colour comparison where a 100 ml column of sample 275 - 295 mm in length is matched with platinum-cobalt solutions.

Technical Data

Applicable Standard ASTM D1209
ISO 6271

Colour Type Transparent

Portability Portable

Delivery Scope

- 1 x Nessleriser Daylight 2000+
- 1 x Hazen D1209 0-30 Disc
- 1 x Hazen D1209 30-70 Disc
- 1 x 1209 Nessleriser body
- 1 x Pair Nessler Cylinders
- 1 x Deionised Water

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebu Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies