

# Lovibond® Water Testing Tintometer® Group



## SensoDirect Con 110



- High measuring accuracy
- Light weight
- Protective casing
- Large digital display

Part Number: 722310

### Different parameters

SensoDirect 110 series meters can be used to measure pH, salt and conductivity.

### Housing

The protective armor does not guarantee a secure grip but also protection against falls. The stand attached to the back of the housing can also be used as a hanger or belt clip.

### "Hold" function included

Data gained is virtually "frozen" on the display by this function. This not only makes it easier to read the results, it also improves reproducibility.

### Automatic battery check

So you do not experience unpleasant surprises with the battery, the level is constantly monitored. This way, you can always change the battery in good time.

### Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry | Pool Public | Pool Services

### SensoDirect Con 110

High-quality, battery-operated handheld instrument for the determination of conductivity.

Variable in use and user-friendly in operation

### Measuring Range

Test Name	Measuring Range
Conductivity	0.001 - 1.999 mS/cm
Conductivity	0.01 - 19.99 mS/cm

### Technical Data

Measuring Range	0,001 - 1,999 mS/cm, 0,01 - 19,99 mS/cm
Auto – OFF	Yes
Power Supply	9 V-block
Portability	Portable
Protection Class	IP 30
Compliance	CE
Dimensions	110 x 34 x 208 mm
Weight	380 g

# Delivery Scope

- Basic instrument
- Battery
- Conductivity sensor
- Instruction manual
- Warranty information

Title	Part Number
Calibration solution 1413 $\mu$ S/cm, 500 ml, traceable to N.I.S.T	722250
Conductivity cell, 1 m cable	724400
Case incl. foam for SensoDirect Con 110	725040
Conductivity Solution (1413 $\mu$ S/cm) - 90 ml - traceable to N.I.S.T.	726654
Conductivity Solution (12.88 mS/cm) - 90 ml - traceable to N.I.S.T.	726684

## Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Germany

## The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

## Tintometer China

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

## Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

## Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brazil

## Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
USA

## Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
India

## Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies