


# Lovibond® Colour Measurement Tintometer® Group



## TA 4 Online-System

Continuous, Online Colour Measurement for Precise Process Control



- Continuous, online colour measurement for precise process control
- Flexibility through full range of industry-standard colour scales
- Seamless integration into production process - correlation with other instruments
- Eliminates time-loss and cost for sampling and lab measurements

Part Number: 178109

### Seamless Integration into Production Process - Correlation with Other Instruments

The Lovibond® TA 4 online system enables you to instantly monitor colour quality throughout the manufacturing process. It is designed to be an easy-to-use monitoring system with the accuracy guaranteed of the Lovibond® brand.

### Eliminates Time-loss and Cost for Sampling and Lab Measurements

The online system provides objective colour data for continuous process control, allowing near real-time process information to be obtained at a low analytical cost. The system can be used for the measurement of constituent concentrations, early detection of trace contaminants and quality assurance analysis. Analytical results can be fed back for automatic process control and optimisation.

### Be Compliant to Internationally Recognised Colour Coordinate Systems

This new generation of online colorimeters utilise diode array spectrophotometers which measure a near real-time response across the spectrum (380 to 780 nm) at 10 nm or less. This spectrophotometric approach allows for the use of internationally recognised colour coordinate systems, such as CIELAB and CIE xzY with the subsequent translation of colour data to industry specific colour scales, as referenced by standardising bodies such as AOCS, DGF, ISO and ASTM.

### Enjoy Ease-of-Use with Touch Screen Input and Display of Graphs

The interactive setup screen allows you to program details of both the reference spectrophotometer and those of the three flow cells. Once in deployment, the display can be set to show different measuring

points and the output scale can be selected. You can view the colour scales in two formats: either as a real-time graph for a single scale at a chosen measurement point or as a set of the latest values for all the scales at all the measurement points.

### Facilitates Multiple Measurement Locations Throughout The Plant

The assembly consists of a Central Control Unit with a reference spectrophotometer. The Control Unit can accept signals from up to 3 flow cells to each of which up to 4 remote signals eg red, yellow, chlorophyll and CIELAB L\* can be connected. The Central Control unit may be housed in a central location up to 45 m away from each cell.

There is no limit as to how many configurations you may install in the plant but each Central Control Unit runs independently and must be monitored separately.

### Get Started with the Lovibond® Team

A team of Lovibond® trained engineers is on-hand to help you get started. With the company's in-depth knowledge of colour science, we can provide advice from colour scales, through recommended path lengths to implementation 'best practice'.

We can also arrange on-site visits to the factory plant for both pre- and post technical meetings, highlighting areas of consideration, advising on implementation and seeing the process through to completion.

## Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Oil and Gas | Pharmaceutical Industry

## Application

Chemicals | Edible Oils and Fats

## TA 4 Online-System

This generation of online colorimeters measures a near real-time response across the spectrum (380 to 780 nm) or less. This spectrophotometric approach allows for the use of internationally recognised colour coordinate systems, such as CIELAB and CIE xzY with the subsequent translation of colour data to industry specific colour scales, as referenced by standardising bodies such as AOCS, DGF, ISO and ASTM.

## Technical Data

|                            |   |
|----------------------------|---|
| <b>Applicable Standard</b> | AOCS Cc 8d-55<br>AOCS Cc 13a-43<br>AOCS Cc 13b-45<br>AOCS Cc 13e-92<br>AOCS Cc 13j-97<br>ASTM D1209<br>ASTM D1544<br>ASTM D6166<br>ASTM E308<br>BS684<br>ISO 6271<br>ISO 15305<br>ISO 27608<br>MS 252 : Part 16<br>MS 817 : Part 12 |
| <b>Color Type</b>          | Transparent   |
| <b>Display</b>             | Embedded PC with touch screen display, internal hard drive Windows XP operating system  |
| <b>Path Length</b>         | 1 inch, 50 mm, 5 1/4 inch   |
| <b>Calibration</b>         | Calibration loop filled with food grade glycerol, automatic calibration program included with software  |
| <b>Internal Storage</b>    | 100,000+ Measurement  |
| <b>Measurement Time</b>    | Less than 5 seconds (depending on length of fiber optic cable)  |
| <b>Spectral Range</b>      | 320 - 780 nm  |
| <b>Illuminants</b>         | CIE Illuminant A  |
| <b>Portability</b>         | Process   |
| <b>Observer</b>            | 2°, 10°   |
| <b>Dimensions</b>          | 500 x 500 x 300 mm  |

## Delivery Scope

Please contact your local Lovibond® representative for details.

---

**Tintometer GmbH**

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Germany

**The Tintometer Limited**

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

**Tintometer China**

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

**Tintometer South East Asia**

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

**Tintometer Brazil**

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brazil

**Tintometer Inc.**

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
USA

**Tintometer India Pvt. Ltd.**

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
India

**Tintometer Spain**

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain